

## **Product List: Polyurethane Gel Elastomers**

Formulation Code	Hardness Range (Shore Durometer)	Component Viscosity	Surface Tack	Variable Ratio	Possible Applications, Note
<u>GK-22R</u>	OO 40 - 70	Low	Very High	Yes	Sticky Pads, Reusable Pressure Sensitive Adhesive. High adhesion strength
<u>GK-7R4</u>	OO 60 - 80	Medium	High	Yes	Sticky Pads, Reusable Pressure Sensitive Adhesive. Low adhesion strength
CGL-3	00 1 - 57	High	High to low	Yes	Low cost filler resin for wrist rest, bicycle saddles, gel pads in film encapsulation
MCP-V40A	00 1 - 30	Low	High to low	Yes	Low rebound, vibration mitigation parts, slow response. Viscoelastic parts
MCG-1	000 68 - 37	Medium high	High to medium	Yes	Microcellular foaming gel. Vibration mitigation for small sensitive parts. Emulating body-fat consistency.
MPC-W44B	000 31 -00 24	Medium high	High	Yes	Filler resin for gel pads used in surgical bed liners, gel cushions, wrist rests, bicycle saddle pads
NTG-10	OO 50 - 60	Low	Low	No	Low tack surface soft parts, Gel shoe insole, grip parts, particle bonding for flexible foam crumbs
<u>SAI-1</u>	00 1 - 00 50	Low	High to low	Yes	Low viscosity resin to make molded parts, motor cycle saddle inserts,
TFG-5	00 5 - 50	Low	High to low	Yes	Low cost, low viscosity filler, tire filler, soft potting, long pot life for filling a larger area

## Continue to next page

Notice: All of the statements, recommendations, suggestions, and data concerning the subject material are based on our laboratory results, and although we believe the same to be reliable, we expressly do not represent, warrant, or guarantee the accuracy, completeness, or reliability of same, or the material or the results to be obtained from the use thereof, neither do we warrant that any such use, either alone or in combination with other materials, shall be free of the rightful claim of any third party by way of INFRINGEMENT or the like, and TANDEM PRODUCTS and NORTHSTAR POLYMERS DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, OF MERCHANTABILITY and FITNESS FOR A PARTICULAR PURPOSE



## **Product List: Polyurethane Gel Elastomers**

Formulation Code	Hardness Range (Shore Durometer)	Component Viscosity	Surface Tack	Variable Ratio	Possible Applications, Note
MGP-V30A	OO 30	Very Low	Low	No	Emulating TPE. Honeycomb gel cushions, Shoe insoles. Contains plasticizer
MGP-V20A	OO 20	Very Low	Low	No	Emulating TPE. Honeycomb gel cushions, Shoe insoles. Contains plasticizer
MGP-V05A	00 5	Very Low	Low	No	Emulating TPE. Shoe insoles. Medical Models, Contains plasticizer
MGP-W50A	000 50	Very Low	Low	No	Emulating TPE. Shoe insoles. Medical Models, Contains plasticizer

Tandem Products, Inc. / DBA Northstar Polymers 3444 Cheatham Avenue, Minneapolis, MN 55406 USA Tel: (612)721-2911

Email: <a href="mailto:info@northstarpolymers.com">info@northstarpolymers.com</a>
Web: <a href="mailto:www.northstarpolymers.com">www.northstarpolymers.com</a>

Notice: All of the statements, recommendations, suggestions, and data concerning the subject material are based on our laboratory results, and although we believe the same to be reliable, we expressly do not represent, warrant, or guarantee the accuracy, completeness, or reliability of same, or the material or the results to be obtained from the use thereof, neither do we warrant that any such use, either alone or in combination with other materials, shall be free of the rightful claim of any third party by way of INFRINGEMENT or the like, and TANDEM PRODUCTS and NORTHSTAR POLYMERS DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, OF MERCHANTABILITY and FITNESS FOR A PARTICULAR PURPOSE